

# STRIP-OFF

Very efficient and biodegradable paint stripper



## Product description

Strip-Off is a multifunctional paint stripper for removing several layers of paint with one treatment.

Strip-Off has been specially developed for the removal of plastic and oil-based paint.

Strip-Off is gel-shaped and can therefore adhere well and have a long effect on almost all surfaces.

Strip-Off is water-based and suitable for indoor use.

## Use

Strip-Off can be used on concrete, stucco, granite, limestone, sandstone, masonry, wood, plastics, glass and metal.

## Characteristics

- Neutral and therefore friendly to most surfaces
- Biodegradable
- Removes several layers of paint
- Strong adhesion and long open time for optimal effect
- User friendly

## Technical data

Odour:	Solvent
Colour:	Yellow
Specific weight:	1,02 kg/L
pH:	8
Contains:	Solvents
Flashpoint:	Not applicable

## Application conditions

Strip-Off can be used in all dry weather conditions.

## Instructions

1. Apply a thick layer of Strip-Off with a brush or roller.
2. Allow the product to work on the surface for 30 minutes up to 36 hours, depending on the temperature and amount of paint layers. Prevent the product from drying. With longer treatment times cover the surface with foil to prevent drying.
3. Jet the dissolved paint with high pressure (50-300 bar) and hot water (70-90°C). Work from bottom to top. Adjust the pressure according to the surface.
4. Scrape away the dissolved paint from fragile surfaces with a putty knife or plastic scraper.
5. After cleaning, rinse the surface thoroughly with clean water.

## Packaging

1 and 10 L

## Consumption

Consumption is 1-4m<sup>2</sup>/L, depending on the surface and amount of paint layers.

## Practical information

- Do not dilute or mix with other products.
- Low temperature can delay the efficacy of the product, adjust the treatment time accordingly.
- Do not apply in direct sunlight or on hot surfaces.
- Use Strip-Off HD to remove strong 2-component paint.
- Collect paint and product residues with Absorbent Rolls.

## Storage

Can be kept for at least 24 months in original unopened packaging.

Store in a cool frost-free place.

## Health and safety

Avoid inhalation, provide adequate ventilation. Avoid skin and eye contact, wear suitable gloves, protective clothing and safety goggles. When in doubt, always consult the safety data sheet or our R&D department.



## Technical support

Mavro is ISO 9001 certified: your guarantee of quality, in terms of products and advice. Our technical consultants and R&D department are always at your service. We are happy to look at your problem or wish with you. Help you with our products or find a solution if it does not yet exist. Call, e-mail or drop by.

Mavro International, Heksekamp 1, 5301 LX Zaltbommel  
T. +31 418 680 680  
E. [info@mavro-int.com](mailto:info@mavro-int.com)  
W. [www.mavro-int.com](http://www.mavro-int.com)

## Disclaimer

This technical data sheet is intended as a guide for the use of the product and is based on the latest development and technology. Because application, processing and environmental conditions are out of our reach, no rights can be derived from this technical data sheet. Mavro International rejects all liability regarding warranty, incorrect application and any damage or consequential damage. The user remains responsible at all times regarding proper use, product choice, application and results.

Edition: August 2024

All previous editions become invalid upon this publication

Product code: 57629